


# **Technical data sheet** Safety light curtain transmitter

## Part no.: 68020113 MLC500T14-1350G



Leuze electronic GmbH + Co. KG 
 The Sensor People
 In der Braike 1, D-73277 Owen/Germany
 Phone: +49 7021 573-0 • Fax: +49 7021 573-199
 eng • 2025-02-17

info@leuze.com • www.leuze.com changes

We reserve the right to make technical

## **Technical data**

#### Basic data

Series	MLC 500
Device type	Transmitter
Cascading	Guest
Contains	2x BT-NC sliding block
Application	Finger protection

#### **Characteristic parameters**

Туре	4, IEC/EN 61496
SIL	3, IEC 61508
SILCL	3, IEC/EN 62061
Mission time T <sub>M</sub>	20 years, EN ISO 13849-1

#### **Protective field data**

Resolution	14 mm
Protective field height	1,350 mm
Operating range	0 6 m

#### **Optical data**

Number of beams	135 Piece(s)
Light source	LED, Infrared
Wavelength	940 nm
Transmitted-signal shape	Pulsed
LED risk group	Exempt group (in acc. with EN 62471:2008)

#### Connection

Number of connections	1 Piece(s)
Connection 1	
Function	Cascade, Host In
	Cascade, Middle Guest In
Type of connection	Cable with connector
Cable length	330 mm
Sheathing material	PUR
Thread size	M12
Material	Plastic
No. of pins	8 -pin

#### Mechanical data

Dimension (W x H x L)	29 mm x 1,364 mm x 53 mm
Housing material	Metal
Metal housing	Aluminum
Lens cover material	Plastic / PMMA
Material of end caps	Diecast zinc
Net weight	1,473 g
Housing color	Yellow, RAL 1021
Type of fastening	Groove mounting
	Mounting brackets
	Swivel mount

#### Environmental data

Ambient temperature, operation	0 55 °C
Ambient temperature, storage	-30 70 °C
Relative humidity (non-condensing)	0 95 %

Leuze

#### Certifications

Degree of protection	IP 65
Protection class	III
Approvals	c TÜV NRTL US
	c UL US
	TÜV Süd
Vibration resistance	50 m/s²
Shock resistance	100 m/s²
US patents	US 6,418,546 B

#### Classification


Customs tariff number	85365019
ECLASS 5.1.4	27272704
ECLASS 8.0	27272704
ECLASS 9.0	27272704
ECLASS 10.0	27272704
ECLASS 11.0	27272704
ECLASS 12.0	27272704
ECLASS 13.0	27272704
ECLASS 14.0	27272704
ECLASS 15.0	27272704
ETIM 5.0	EC002549
ETIM 6.0	EC002549
ETIM 7.0	EC002549
ETIM 8.0	EC002549
ETIM 9.0	EC002549
ETIM 10.0	EC002549

## **Dimensioned drawings**

Leuze

All dimensions in millimeters

## Calculation of the effective protective field height $H_{PFE} = H_{PFN} + B + C$



 $H_{PFE}$  Effective protective field height = 1362 mm

С

R

- H<sub>PFN</sub> Nominal protective field height = 1350 mm
- Total height = 1364 mm А
- В 6 mm

Effective protective field height  ${\rm H}_{\rm PFE}$  goes beyond the dimensions of the optics area to the outer borders of the circles labeled with R.

## **Electrical connection**

#### **Connection 1**

Function	Cascade, Host In
	Cascade, Middle Guest In
Type of connection	Cable with connector
Cable length	330 mm
Sheathing material	PUR
Cable color	Black
Type of stranding	Pair stranding (twisted pair)
Wire cross section	0.14 mm <sup>2</sup>
Thread size	M12
Туре	Male
Material	Plastic
No. of pins	8 -pin
Encoding	A-coded

### Suitable receivers

 Part no.	Designation	Article	Description
68021113	MLC520R14-1350G	Safety light curtain receiver	Resolution: 14 mm Protective field height: 1,350 mm Response time: 29 ms Connection: Cable with connector, M12, Plastic, 8 -pin, 330 mm, PUR

## Part number code

#### Part designation: MLCxyy-za-hhhhei-ooo



MLC	Safety light curtain
x	Series 3: MLC 300 5: MLC 500
уу	Function classes         00: transmitter         01: transmitter (AIDA)         02: transmitter with test input         10: basic receiver - automatic restart         11: basic receiver - automatic restart (AIDA)         20: standard receiver - EDM/RES selectable         30: Extended receiver blanking/muting or gating         35: Extended receiver – Gating
z	Device type T: transmitter R: receiver
а	Resolution         14: 14 mm         20: 20 mm         30: 30 mm         40: 40 mm         90: 90 mm
hhhh	Protective field height 150 … 3000: from 150 mm to 3000 mm
e	Host/Guest (optional) H: Host MG: Middle Guest G: Guest
i	Interface (optional) /A: AS-i
000	Option //: high Vibration-proof EX2: explosion protection (zones 2 + 22) SPG: Smart Process Gating SPG RR: Smart Process Gating – Reduced resolution
	Note
	∜ A list with all available device types can be found on the Leuze website at www.leuze.com.

## Notes

/!\

\!

#### Observe intended use!

The product may only be put into operation by competent persons.

## Accessories

# Leuze

## Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	429278	CB-M12-2000E-8TP	Interconnection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 8 -pin Connection 2: Connector, M12, Axial, Male, A-coded, 8 -pin Shielded: Yes Cable length: 2,000 mm Sheathing material: PUR

## Mounting technology - Mounting brackets

	Part no.	Designation	Article	Description
1111	429006	BT-2L-HG	Mounting device set	Mounting bracket, at device: Screw type Material: Metal

## Mounting technology - Swivel mounts

	Part no.	Designation	Article	Description
P.Q.	429395	BT-2HF-G	Mounting bracket set	Fastening, at system: Through-hole mounting Mounting bracket, at device: Clampable Type of mounting device: Turning, 360° Material: Metal, Plastic

## Alignment aids

 Part no.	Designation	Article	Description
520101	AC-ALM-M	Alignment aid	Housing material: Plastic

## Services

	Part no.	Designation	Article	Description
$\bigcirc$	S981050	CS40-I-140	Safety inspection	Details: Checking of a safety light barrier application in accordance with current standards and guidelines. Inclusion of the device and machine data in a database, production of a test log per application. Conditions: It must be possible to stop the machine, support provided by customer's employees and access to the machine for Leuze employees must be ensured.
y, U	S981046	CS40-S-140	Start-up support	Details: For safety devices including stopping time measurement and initial inspection. Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses.

## Accessories





♦ A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.